

ステンレス薄板 対応表 → A

SUS304						SUS304					
仕上	厚さ	幅	長さ	枚重量		仕上	厚さ	幅	長さ	枚重量	
2B	0.3	× 1000	× 2000	4.76		片研SPV	0.3	× 1000	× 2000	4.76	
2B	0.4	× 1000	× 2000	6.34		片研SPV	0.4	× 1000	× 2000	6.34	
2B	0.5	× 1000	× 2000	7.93		片研SPV	0.5	× 1000	× 2000	7.93	
2B	0.5	× 1219	× 2438	11.8		片研SPV	0.5	× 1219	× 2438	11.8	
2B	0.6	× 1000	× 2000	9.52		片研SPV	0.6	× 1000	× 2000	9.5	
2B	0.6	× 1219	× 2438	14.1		片研SPV	0.6	× 1219	× 2438	14.1	
2B	0.7	× 1000	× 2000	11.1		片研SPV	0.7	× 1000	× 2000	11.1	
2B	0.8	× 1000	× 2000	12.7		片研SPV	0.8	× 1000	× 2000	12.7	
2B	0.8	× 1219	× 2438	18.9		片研SPV	0.8	× 1219	× 2438	18.9	
2B	1.0	× 1000	× 2000	15.9		片研SPV	1.0	× 1000	× 2000	15.9	
2B	1.0	× 1219	× 2438	23.6		片研SPV	1.0	× 1219	× 2438	23.6	
2B	1.0	× 1524	× 3048	36.8		片研SPV	1.0	× 1524	× 3048	36.8	
2B	1.2	× 1000	× 2000	19.0		片研SPV	1.2	× 1000	× 2000	19.0	
2B	1.2	× 1219	× 2438	28.3		片研SPV	1.2	× 1219	× 2438	28.3	
2B	1.2	× 1524	× 3048	44.2		片研SPV	1.2	× 1524	× 3048	44.2	
2B	1.5	× 1000	× 2000	23.8		片研SPV	1.5	× 1000	× 2000	23.8	
2B	1.5	× 1219	× 2438	35.4		片研SPV	1.5	× 1219	× 2438	35.4	
2B	1.5	× 1524	× 3048	55.3		片研SPV	1.5	× 1524	× 3048	55.3	
2B	1.5	× 1524	× 4000	72.5		片研SPV	1.5	× 1524	× 4000	72.5	
2B	2.0	× 1000	× 2000	31.7		片研SPV	2.0	× 1000	× 2000	31.7	
2B	2.0	× 1219	× 2438	47.1		片研SPV	2.0	× 1219	× 2438	47.1	
2B	2.0	× 1524	× 3048	73.7		片研SPV	2.0	× 1524	× 3048	73.7	
2B	2.0	× 1524	× 4000	96.7		片研SPV	2.0	× 1524	× 4000	96.7	
2B	2.5	× 1000	× 2000	39.7		片研SPV	2.5	× 1000	× 2000	39.7	
2B	2.5	× 1219	× 2438	58.9		片研SPV	2.5	× 1219	× 2438	58.9	
2B	2.5	× 1524	× 3048	92.1		片研SPV	2.5	× 1524	× 3048	92.1	
2B	3.0	× 1000	× 2000	47.6		片研SPV	3.0	× 1000	× 2000	47.6	
2B	3.0	× 1219	× 2438	70.7		片研SPV	3.0	× 1219	× 2438	70.7	
2B	3.0	× 1524	× 3048	111		片研SPV	3.0	× 1524	× 3048	111	
2B	3.0	× 1524	× 4000	145.9		片研SPV	3.0	× 1524	× 4000	145.9	
NO1	3.0	× 1000	× 2000	47.6							
NO1	3.0	× 1219	× 2438	70.7							
NO1	3.0	× 1524	× 3048	111							
NO1	3.0	× 1524	× 4000	145.9							

ステンレス薄板 対応表 → A

SUS304						SUS304							
仕上	厚さ	幅	長さ	枚重量		仕上	厚さ	幅	長さ	枚重量			
両研SPV	0.3	×	1000	×	2000	4.76	HLSPV	0.5	×	1000	×	2000	7.93
両研SPV	0.4	×	1000	×	2000	6.34	HLSPV	0.6	×	1000	×	2000	9.52
両研SPV	0.5	×	1000	×	2000	7.93	HLSPV	0.8	×	1000	×	2000	12.7
両研SPV	0.5	×	1219	×	2438	11.8	HLSPV	0.8	×	1219	×	2438	18.9
両研SPV	0.6	×	1000	×	2000	9.52	HLSPV	1.0	×	1000	×	2000	15.9
両研SPV	0.6	×	1219	×	2438	14.1	HLSPV	1.0	×	1219	×	2438	23.6
両研SPV	0.7	×	1000	×	2000	11.1	HLSPV	1.2	×	1000	×	2000	19.0
両研SPV	0.8	×	1000	×	2000	12.7	HLSPV	1.2	×	1219	×	2438	28.3
両研SPV	0.8	×	1219	×	2438	18.9	HLSPV	1.2	×	1524	×	3048	44.2
両研SPV	1.0	×	1000	×	2000	15.9	HLSPV	1.5	×	1000	×	2000	23.8
両研SPV	1.0	×	1219	×	2438	23.6	HLSPV	1.5	×	1219	×	2438	35.4
両研SPV	1.0	×	1524	×	3048	36.8	HLSPV	1.5	×	1524	×	3048	55.3
両研SPV	1.2	×	1000	×	2000	19.0	HLSPV	1.5	×	1524	×	4000	72.5
両研SPV	1.2	×	1219	×	2438	28.3	HLSPV	2.0	×	1000	×	2000	31.7
両研SPV	1.2	×	1524	×	3048	44.2	HLSPV	2.0	×	1219	×	2438	47.1
両研SPV	1.5	×	1000	×	2000	23.8	HLSPV	2.0	×	1524	×	3048	73.7
両研SPV	1.5	×	1219	×	2438	35.4	HLSPV	2.0	×	1524	×	4000	96.7
両研SPV	1.5	×	1524	×	3048	55.3	HLSPV	3.0	×	1000	×	2000	47.6
両研SPV	1.5	×	1524	×	4000	72.5	HLSPV	3.0	×	1219	×	2438	70.7
両研SPV	2.0	×	1000	×	2000	31.7	HLSPV	3.0	×	1524	×	3048	111
両研SPV	2.0	×	1219	×	2438	47.1	HLSPV	3.0	×	1524	×	4000	145.9
両研SPV	2.0	×	1524	×	3048	73.7							
両研SPV	2.0	×	1524	×	4000	96.7							
両研SPV	2.5	×	1000	×	2000	39.7							
両研SPV	2.5	×	1219	×	2438	58.9							
両研SPV	2.5	×	1524	×	3048	92.1							
両研SPV	3.0	×	1000	×	2000	47.6							
両研SPV	3.0	×	1219	×	2438	70.7							
両研SPV	3.0	×	1524	×	3048	111							
両研SPV	3.0	×	1524	×	4000	145.9							

ステンレス薄板 対応表 → A

SUS430						SUS430					
仕上	厚さ	幅	長さ	枚重量		仕上	厚さ	幅	長さ	枚重量	
2B	0.3	× 1000	× 2000	4.62		片研SPV	0.3	× 1000	× 2000	4.62	
2B	0.4	× 1000	× 2000	6.16		片研SPV	0.4	× 1000	× 2000	6.16	
2B	0.5	× 1000	× 2000	7.70		片研SPV	0.5	× 1000	× 2000	7.70	
2B	0.6	× 1000	× 2000	9.24		片研SPV	0.6	× 1000	× 2000	9.24	
2B	0.7	× 1000	× 2000	10.8		片研SPV	0.7	× 1000	× 2000	10.8	
2B	0.8	× 1000	× 2000	12.3		片研SPV	0.8	× 1000	× 2000	12.3	
2B	0.8	× 1219	× 2438	18.3		片研SPV	0.8	× 1219	× 2438	18.3	
2B	1.0	× 1000	× 2000	15.4		片研SPV	1.0	× 1000	× 2000	15.4	
2B	1.0	× 1219	× 2438	22.9		片研SPV	1.0	× 1219	× 2438	22.9	
2B	1.2	× 1000	× 2000	18.5		片研SPV	1.2	× 1000	× 2000	18.5	
2B	1.2	× 1219	× 2438	27.5		片研SPV	1.2	× 1219	× 2438	27.5	
2B	1.5	× 1000	× 2000	23.1		片研SPV	1.5	× 1000	× 2000	23.1	
2B	1.5	× 1219	× 2438	34.3		片研SPV	1.5	× 1219	× 2438	34.3	
2B	2.0	× 1000	× 2000	30.8		片研SPV	2.0	× 1000	× 2000	30.8	
2B	2.0	× 1219	× 2438	45.8		片研SPV	2.0	× 1219	× 2438	45.8	
2B	2.5	× 1000	× 2000	38.5		片研SPV	2.5	× 1000	× 2000	38.5	
2B	3.0	× 1000	× 2000	46.2		片研SPV	3.0	× 1000	× 2000	46.2	
2B	3.0	× 1219	× 2438	68.6		片研SPV	3.0	× 1219	× 2438	68.6	

ステンレス薄板 対応表 → A

SUS430						
仕上	厚さ		幅		長さ	枚重量
両研SPV	0.3	×	1000	×	2000	4.62
両研SPV	0.4	×	1000	×	2000	6.16
両研SPV	0.5	×	1000	×	2000	7.70
両研SPV	0.6	×	1000	×	2000	9.24
両研SPV	0.7	×	1000	×	2000	10.8
両研SPV	0.8	×	1000	×	2000	12.3
両研SPV	0.8	×	1219	×	2438	18.3
両研SPV	1.0	×	1000	×	2000	15.4
両研SPV	1.0	×	1219	×	2438	22.9
両研SPV	1.2	×	1000	×	2000	18.5
両研SPV	1.2	×	1219	×	2438	27.5
両研SPV	1.5	×	1000	×	2000	23.1
両研SPV	1.5	×	1219	×	2438	34.3
両研SPV	2.0	×	1000	×	2000	30.8
両研SPV	2.0	×	1219	×	2438	45.8
両研SPV	2.5	×	1000	×	2000	38.5
両研SPV	3.0	×	1000	×	2000	46.2
両研SPV	3.0	×	1219	×	2438	68.6